



## GUY-HOOK ATTACHMENT, 12,400 lbs. STRENGTH, 5/8in BOLT SIZE with INTEGRAL LAG SPUR

By CHANCE Utility  
Catalog # [GH5ILS](#)

Cast ductile iron guy-hook attachment for deadending guy or messenger wire. Industry slang is Ram's Head.



### Features

- Maximum strand size is 7/16"
- Backside surface cleats increase stability in wood pole installations
- 2-1/2" base width x 4-3/4" length
- Rating increases to 13,550 lbs. with ASTM A-307 thru-bolts
- Ductile Iron per ASTM A-536
- Galvanized per ASTM A-153
- Manufactured to specification IEEE C135.90

### General

Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
Tensile Strength	12400 lb.
UPC	096359036739

### Dimensions

Distance From Pole	N/A
Weight	1.43 lb

### Logistics

Pallet Quantity	1200
-----------------	------

### Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)

[Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)

[Sales Drawings - Guy Hook \(SAGH5ILS\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-GH5ILS-SPEC-EN | REV 4/2023