



**GUY-HOOK ATTACHMENT, 12,400  
lbs. STRENGTH, 5/8in BOLT SIZE  
with 9/16in LAG HOLE, w/o  
BACKSIDE CLEATS**

By Chance  
Catalog # [GH5N](#)



Cast ductile iron guy-hook attachment for deadending guy or messenger wire. Industry slang is Ram's Head.

**Features**

- Maximum strand size is 7/16"
- Smooth backside surface (less cleats) for non-wood pole installations
- 2-1/2" base width x 4-3/4" length
- Rating increases to 13,550 lbs. with ASTM A-307 thru-bolts
- Ductile Iron per ASTM A-536
- Galvanized per ASTM A-153
- Manufactured to specificaition IEEE C135.90

**General**

Catalog Number	GH5N
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Ductile Iron, ASTM A-536
UPC	096359494782

**Dimensions**

Distance From Pole	N/A
Weight	1.36 lb

**Certifications And Compliance**

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

**Logistics**

Carton Quantity	25
Pallet Quantity	1200

**Product Assets**

- [Sales Drawings - Guy Hook 5/8" Bolt](#)
- [Sales Drawings - Guy Hook](#)
- [Specifications - GH5N](#)