



GUY-HOOK ATTACHMENT, 18,350 lbs. STRENGTH, 3/4in BOLT SIZE with 9/16in LOWER HOLE

By Chance
Catalog # [GH6](#)

Cast ductile iron guy-hook attachment for deadending guy or messenger wire. Industry slang is Ram's Head.



Features

- Maximum strand size is 1/2"
- Backside surface cleats increase stability in wood pole installations
- 2-1/2" base width x 4-3/4" length
- Ductile Iron per ASTM A-536
- Galvanized per ASTM A-153
- Manufactured to specification IEEE C135.90

General

Catalog Number	GH6
Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
Tensile Strength	18350 lb.
UPC	096359036746

Dimensions

Dimensions	5.000 in x 3.600 in x 1.750 in
Distance From Pole	N/A
Height	1.75 in
Length	5 in
Weight	1.25 lb
Width	3.6 in

Logistics

Pallet Quantity	1200
-----------------	------

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)
- [Sales Drawings - Guy Hook 3/4" Bolt](#)
- [Sales Drawings - Guy Hook](#)



A Hubbell brand