



GUY-HOOK ATTACHMENT, 18,350 lbs. STRENGTH, 3/4in BOLT SIZE with 9/16in LOWER HOLE and w/o BACKSIDE CLEATS

By Chance
Catalog # [GH6N](#)

Cast ductile iron guy-hook attachment for deadending guy or messenger wire. Industry slang is Ram's Head.



Features

- Maximum strand size is 1/2"
- Smooth backside surface (less cleats) for non-wood pole installations
- 2-1/2" base width x 4-3/4" length
- Ductile Iron per ASTM A-536
- Galvanized per ASTM A-153
- Manufactured to specification IEEE C135.90

General

Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
UPC	096359494799

Dimensions

Distance From Pole	N/A
Weight	1.25 lb

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Sales Drawings - Guy Hook](#)
- [Sales Drawings - Guy Hook 3/4" Bolt](#)