



GUY-HOOK ATTACHMENT, 25,400 lbs. STRENGTH, 7/8in BOLT SIZE with 9/16in & 13/16in LOWER HOLES

By Chance
Catalog # GH6X

Cast ductile iron guy-hook attachment for deadending guy or messenger wire. Industry slang is Ram's Head.



Features

- Maximum strand size is 3/4"
- Backside surface cleats increase stability in wood pole installations
- 2-3/4" base width x 5-11/16" length
- Ductile Iron per ASTM A-536
- Galvanized per ASTM A-153
- Manufactured to specification IEEE C135.90

General

Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
Tensile Strength	25400 lb.
UPC	096359036777

Dimensions

Distance From Pole	N/A
Weight	1.89 lb

Logistics

Pallet Quantity	1000
-----------------	------

Product Assets

[Catalogs - Communications Catalog](#)
[Sales Drawings - Guy Hook](#)