



# 12" 16K Guy Strain, Clevis / Clevis + 2 Rollers

By Chance  
Catalog # [GS16012CC2](#)

12" Fiberglass Guy Strain; 16,000 lb Series; Clevis / Clevis + 2 Rollers

## Features

- 5/8" diameter fiberglass rod
- End fittings are hot dip galvanized ductile iron

## General

|                            |                             |
|----------------------------|-----------------------------|
| Catalog Number             | GS16012CC2                  |
| Description - End Fitting  | Clevis - Clevis - 2 Rollers |
| Material                   | Fiberglass - Veiled Rod     |
| Strength Rating - Ultimate | 16000 lb                    |
| Tensile Strength           | 16000 lb.                   |
| UPC                        | 096359036821                |

## Dimensions

|                       |          |
|-----------------------|----------|
| Diameter - Rod / Tube | 0.625 in |
| Length                | 12 in    |



|   |         |
|---|---------|
| Length - Clevis Pin Center to Clevis Bottom | 1.38 in |
| Mounting Bolt Spacing                       | 20 in   |
| Weight                                      | 2.8 lb  |

## Logistics

|                  |     |
|------------------|-----|
| Pallet Quantity  | 720 |
| Standard Package | 10  |

## Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Literature - Silicone Coated Guy Strains](#)
- [Literature - CHANCE® Silicone Coated Guy Strains](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant](#)
- [Sales Drawings - Guy Strain, 16 K Clevis, 1 Roller](#)
- [Specifications - GS16012CC2](#)



A Hubbell brand