



12" 16K Guy Strain, Clevis / Thimble-Eye

By Chance

Catalog # [GS16012CP](#)

12" Fiberglass Guy Strain; 16,000 lb Series; Clevis / Thimble-Eye



Features

- 5/8" diameter fiberglass rod
- End fittings are hot dip galvanized ductile iron

General

Catalog Number	GS16012CP
Description - End Fitting	Clevis - Thimble-Eye
Material	Fiberglass - Veiled Rod
Strength Rating - Ultimate	16000 lb
Tensile Strength	16000 lb.
UPC	096359036845

Dimensions

Diameter - Rod / Tube	0.625 in
Dimensions	12 in x 2.75 in x 1.69 in
Height	1.69 in
Length	12 in
Length - Clevis Pin Center to Clevis Bottom	1.38 in

Mounting Bolt Spacing	21.3 in
Weight	2.57 lb
Width	2.75 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	720
Standard Package	10

Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Catalogs - CHANCE® Fiberglass Construction Products](#)
- [Literature - CHANCE® Silicone Coated Guy Strains](#)
- [Literature - Silicone Coated Guy Strains](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant](#)
- [Sales Drawings - 16K CP Guy Strains](#)
- [Specifications - GS16012CP](#)