



24" 16K Guy Strain, Clevis / Thimble-Eye

By CHANCE Utility
Catalog # [GS16024CP](#)

24" Fiberglass Guy Strain; 16,000 lb Series; Clevis / Thimble-Eye



*Representative Image

General

Description - End Fitting	Clevis - Thimble-Eye
Material	Fiberglass - Veiled Rod
Strength Rating - Ultimate	16000 lb
Tensile Strength	16000 lb.
UPC	096359036982

Dimensions

Diameter - Rod / Tube	0.625 in
Length	24.00 in
Length - Clevis Pin Center to Clevis Bottom	1.38 in
Mounting Bolt Spacing	32.00 in
Weight	3.1 lb

Logistics

Standard Package	10
------------------	----

Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-6\)](#)
- [Literature - CHANCE® Silicone Coated Guy Strains \(CENT-CHN-CC-GUY-STRAINS-SF-EN-2022-00191\)](#)
- [Literature - Silicone Coated Guy Strains \(SF09146E\)](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant \(SF09147E\)](#)
- [Sales Drawings - 16K CP Guy Strains](#)
- [Technical Solutions - CH-GS16024CP-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-GS16024CP-SPEC-EN | REV 1/2024