



54" 16K Guy Strain, Clevis / Clevis + 2 Rollers

By CHANCE Utility
Catalog # [GS16054CC2](#)

54" Fiberglass Guy Strain; 16,000 lb Series; Clevis / Clevis + 2
Rollers



*Representative Image

General

Description - End Fitting	Clevis - Clevis - 2 Rollers
Material	Fiberglass - Veiled Rod
Strength Rating - Ultimate	16000 lb
Tensile Strength	16000 lb.
UPC	096359037194

Dimensions

Diameter - Rod / Tube	0.625 in
Length	54.00 in
Length - Clevis Pin Center to Clevis Bottom	1.38 in
Mounting Bolt Spacing	62.00 in
Weight	3.7 lb

Logistics

Pallet Quantity	240
Standard Package	10

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-5\)](#)

[Catalogs - CHANCE® Fiberglass Construction Products \(Catalog 12\)](#)

[Literature - CHANCE® Silicone Coated Guy Strains \(CENT-CHN-CC-GUY-STRAINS-SF-EN-2022-00191\)](#)

[Literature - Silicone Coated Guy Strains \(SF09146E\)](#)

[Literature - Silicone Coated Guy Strains - CSA Compliant \(SF09147E\)](#)

[Sales Drawings - Guy Strain, 16 K Clevis, 1 Roller](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-GS16054CC2-SPEC-EN | REV 4/2023