



78" 16K Guy Strain, Clevis / Thimble-Eye

By CHANCE Utility
Catalog # [GS16078CP](#)

78" Fiberglass Guy Strain; 16,000 lb Series; Clevis / Thimble-Eye



*Representative Image

General

Description - End Fitting	Clevis - Thimble-Eye
Material	Fiberglass - Veiled Rod
Strength Rating - Ultimate	16000 lb
Tensile Strength	16000 lb.
UPC	096359037309

Dimensions

Diameter - Rod / Tube	0.625 in
Length	78.00 in
Length - Clevis Pin Center to Clevis Bottom	1.38 in
Mounting Bolt Spacing	86.00 in
Weight	4.2 lb

Logistics

Pallet Quantity	240
Standard Package	10

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-6\)](#)

[Catalogs - CHANCE® Fiberglass Construction Products \(Catalog 12\)](#)

[Literature - CHANCE® Silicone Coated Guy Strains \(CENT-CHN-CC-GUY-STRAINS-SF-EN-2022-00191\)](#)

[Literature - Silicone Coated Guy Strains \(SF09146E\)](#)

[Literature - Silicone Coated Guy Strains - CSA Compliant \(SF09147E\)](#)

[Sales Drawings - 16K CP Guy Strains](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-GS16078CP-SPEC-EN | REV 4/2023