



24" 30K Silicone Coated Guy Strain, Clevis / Clevis + 2 Rollers

By CHANCE Utility
Catalog # [GS30024CC2SC](#)

24" Silicone Coated Fiberglass Guy Strain; 30,000 lb Series;
Clevis / Clevis + 2 Rollers



*Representative Image

General

Description - End Fitting	Clevis - Clevis - 2 Rollers
Material	Fiberglass - Silicone Coated Rod
Tensile Strength	30000 lb.

Dimensions

Diameter - Rod / Tube	0.750 in
Length	24.00 in
Length - Clevis Pin Center to Clevis Bottom	2.25 in
Weight	6.5 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalog Page - Page_12-14](#)
- [Literature - CHANCE® Silicone Coated Guy Strains \(CENT-CHN-CC-GUY-STRAINS-SF-EN-2022-00191\)](#)
- [Literature - Silicone Coated Guy Strains \(SF09146E\)](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant \(SF09147E\)](#)
- [Sales Drawings - 30K Guy Strain 2-Roller Silicone Coated Rod \(SAGS30XXXCC2SC\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-GS30024CC2SC-SPEC-EN | REV 1/2024