



78" 30K Silicone Coated Guy Strain, Clevis / Clevis + 2 Rollers

By CHANCE Utility
Catalog # [GS30078CC2SC](#)

78" Silicone Coated Fiberglass Guy Strain; 30,000 lb Series;
Clevis / Clevis + 2 Rollers



*Representative Image

General

Description - End Fitting	Clevis - Clevis - 2 Rollers
Material	Fiberglass - Silicone Coated Rod
Tensile Strength	30000 lb.
UPC	096359732211

Dimensions

Diameter - Rod / Tube	0.750 in
Length	78.00 in
Length - Clevis Pin Center to Clevis Bottom	2.25 in
Weight	8.2 lb

Logistics

Pallet Quantity	125
Standard Package	1

Product Assets

[Catalog Page - Page_12-14](#)
[Literature - CHANCE® Silicone Coated Guy Strains \(CENT-CHN-CC-GUY-STRAINS-SF-EN-2022-00191\)](#)
[Literature - Silicone Coated Guy Strains \(SF09146E\)](#)
[Literature - Silicone Coated Guy Strains - CSA Compliant \(SF09147E\)](#)
[Sales Drawings - 30K Guy Strain 2-Roller Silicone Coated Rod \(SAGS30XXXCC2SC\)](#)
[Technical Solutions - CH-GS30078CC2SC-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-GS30078CC2SC-SPEC-EN | REV 1/2024