



## 84" 30K Silicone Coated Guy Strain, Clevis / Clevis + 2 Rollers

By CHANCE Utility  
Catalog # [GS30084CC2SC](#)

84" Silicone Coated Fiberglass Guy Strain; 30,000 lb Series;  
Clevis / Clevis + 2 Rollers



\*Representative Image

### General

Description - End Fitting	Clevis - Clevis - 2 Rollers
Material	Fiberglass - Silicone Coated Rod
Tensile Strength	30000 lb.

### Dimensions

Diameter - Rod / Tube	0.750 in
Length	84.00 in
Length - Clevis Pin Center to Clevis Bottom	2.25 in
Weight	8.4 lb

### Logistics

Standard Package	1
------------------	---

### Product Assets

- [Catalog Page - Page\\_12-14](#)
- [Literature - CHANCE® Silicone Coated Guy Strains \(CENT-CHN-CC-GUY-STRAINS-SF-EN-2022-00191\)](#)
- [Literature - Silicone Coated Guy Strains \(SF09146E\)](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant \(SF09147E\)](#)
- [Sales Drawings - 30K Guy Strain 2-Roller Silicone Coated Rod \(SAGS30XXXCC2SC\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-GS30084CC2SC-SPEC-EN | REV 1/2024