



## 108" 30K Guy Strain, Clevis / Clevis

By CHANCE Utility  
Catalog # [GS30108CC](#)

108" Fiberglass Guy Strain; 30,000 lb Series; Clevis / Clevis



\*Representative Image

### General

Description - End Fitting	Clevis - Clevis
Material	Fiberglass - Veiled Rod
Strength Rating - Ultimate	30000 lb
Tensile Strength	30000 lb.

### Dimensions

Diameter - Rod / Tube	0.750 in
Length	108.00 in
Length - Clevis Pin Center to Clevis Bottom	2.25 in
Mounting Bolt Spacing	120.00 in
Weight	9.2 lb

### Logistics

Carton Quantity	5
Standard Package	1

### Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-14\)](#)
- [Literature - CHANCE® Silicone Coated Guy Strains \(CENT-CHN-CC-GUY-STRAINS-SF-EN-2022-00191\)](#)
- [Literature - Silicone Coated Guy Strains \(SF09146E\)](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant \(SF09147E\)](#)
- [Sales Drawings - 30K Guy Strain \(SA\\_GS30xxxCCx\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-GS30108CC-SPEC-EN | REV 1/2024