



108" 30K Guy Strain, Clevis / Clevis + 2 Rollers

By Chance
Catalog # [GS30108CC2](#)

108" Fiberglass Guy Strain; 30,000 lb Series; Clevis / Clevis + 2 Rollers

Features

- 3/4" diameter fiberglass rod
- End fittings are hot dip galvanized ductile iron

General

Catalog Number	GS30108CC2
Description - End Fitting	Clevis - Clevis - 2 Rollers
Material	Fiberglass - Veiled Rod
Strength Rating - Ultimate	30000 lb
Tensile Strength	30000 lb.
UPC	096359729631

Dimensions

Diameter - Rod / Tube	0.75 in
Length	108 in



*Representative Image

Length - Clevis Pin Center to Clevis Bottom	2.25 in
Mounting Bolt Spacing	120 in
Weight	9.2 lb

Logistics

Pallet Quantity	125
Standard Package	1

Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Literature - CHANCE® Silicone Coated Guy Strains](#)
- [Literature - Silicone Coated Guy Strains](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant](#)
- [Sales Drawings - 30K Guy Strain](#)
- [Specifications - GS30108CC2](#)