



# 108" 30K Guy Strain, Thimble-Eye / Thimble-Eye

By Chance  
Catalog # [GS30108PP](#)

108" Fiberglass Guy Strain; 30,000 lb Series; Thimble-Eye / Thimble-Eye

## Features

- 3/4" diameter fiberglass rod
- End fittings are hot dip galvanized ductile iron

## General

Catalog Number	GS30108PP
Description - End Fitting	Thimble-Eye - Thimble-Eye
Material	Fiberglass - Veiled Rod
Strength Rating - Ultimate	30000 lb
Tensile Strength	30000 lb.
UPC	096359724933

## Dimensions

Diameter - Rod / Tube	0.75 in
Length	108 in



\*Representative Image

Length - Clevis Pin Center to Clevis Bottom	3.08 in
Mounting Bolt Spacing	122 in
Weight	9.2 lb

## Logistics

Pallet Quantity	125
Standard Package	1

## Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Literature - Silicone Coated Guy Strains](#)
- [Literature - CHANCE® Silicone Coated Guy Strains](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant](#)
- [Sales Drawings - Guy Strain, 30K Thimble eye - Thimble eye](#)
- [Specifications - GS30108PP](#)



A Hubbell brand