



## 120" 30K Guy Strain, Clevis / Clevis + 2 Rollers

By Chance  
Catalog # [GS30120CC2](#)

120" Fiberglass Guy Strain; 30,000 lb Series; Clevis / Clevis + 2 Rollers



\*Representative Image

### General

Description - End Fitting	Clevis - Clevis - 2 Rollers
Material	Fiberglass - Veiled Rod
Strength Rating - Ultimate	30000 lb
Tensile Strength	30000 lb.
UPC	096359511243

### Dimensions

Diameter - Rod / Tube	0.75 in
Length	120 in
Length - Clevis Pin Center to Clevis Bottom	2.25 in
Mounting Bolt Spacing	132 in
Weight	9.6 lb

### Logistics

Standard Package	1
------------------	---

### Product Assets

- [Catalog Page - CHANCE® Fiberglass Construction Products](#)
- [Literature - Silicone Coated Guy Strains](#)
- [Literature - CHANCE® Silicone Coated Guy Strains](#)
- [Literature - Silicone Coated Guy Strains - CSA Compliant](#)
- [Sales Drawings - 30K Guy Strain](#)