



EXTENSION LINK, 14in LENGTH, 15,000lbs MINIMUM STRENGTH

By Chance
Catalog # [L14](#)

Extension links provide additional clearance for deadend and corner installations.

Features

- 11/16" dia. link hole
- 13/16" clevis opening
- 5/8" dia. clevis pin
- Ductile iron per ASTM A536, galvanized per ASTM A-153

General

Catalog Number	L14
Coating	Galvanized, ASTM A-153
Material	Ductile Iron, ASTM A-536
Tensile Strength	15,000 lb
Type	Extensions
UPC	096359041818

Dimensions

Dimensions	15.375 in x 2.125 in x 1.500 in
Distance From Pole	N/A
Height	1.5 in
Length	15.375 in
Weight	2.35 lb
Width	2.125 in

Logistics

Pallet Quantity	960
-----------------	-----

Product Assets

- [Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)
- [Sales Drawings - Extension Link](#)
- [Specifications - L14](#)



A Hubbell brand