



0.6 A, Type Slo-Fast Fuselinks, 26" Length, Solid Head

By CHANCE Utility
Catalog # MOD6SF

0.6 amp, Type SloFast Cutout fuselink with a 26" (660.4mm) pigtail.

Features

- Comparable to Cooper/Kearney Type X fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Dual element design specific for tranformer protection
- Slow portion of time current characteristic curve closely matesches transformers safe loading cureve
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Fuse Head Style	Solid
Fuselink Type	Type SloFast
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359042129



Dimensions

Length - Fuselink	26" (660.4mm)
-------------------	---------------

Electrical Ratings

Amperage Rating	0.6 A
-----------------	-------

Logistics

Standard Package	10
------------------	----

Product Assets

- [Catalogs - Fuse Links \(10B\)](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type SloFast](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type SloFast](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type SF Solid & Removable HD \(PSSASFFUSELINK\)](#)
- [Test Documents - SloFast Min Melt](#)
- [Test Documents - SloFast Total Clear](#)



A proud member of the Hubbell Family.