



0.7 A, Type Slo-Fast Fuselinks, 23" Length, Removable Head

By Chance

Catalog # [MOD7SFA23](#)

0.7 amp, Type SloFast Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.


Features

- Comparable to Cooper/Kearney Type X fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Dual element design specific for transformer protection
- Slow portion of time current characteristic curve closely matches transformers safe loading curve
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	MOD7SFA23
Fuse Head Style	Removable
Fuselink Type	Type SloFast
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359042198

Dimensions



Length - Fuselink	23" (584.2mm)
Weight	0.098 lb

Electrical Ratings

Amperage Rating	0.7 A
-----------------	-------

Logistics

Pallet Quantity	4800
Standard Package	10

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type SloFast](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type SloFast](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type SF Solid & Removable HD](#)
- [Specifications - MOD7SFA23](#)
- [Test Documents - SloFast Total Clear](#)
- [Test Documents - SloFast Min Melt](#)



A Hubbell brand