



100 A, Type K (ANSI) fuselinks, 26" Length, Removable Head

By Chance
Catalog # [M100KA](#)

100 amp, Type K (ANSI) Cutout fuselink with a 26" (660.4mm) pigtail and a removable buttonhead.

Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M100KA
Fuse Head Style	Removable
Fuselink Type	Type K (ANSI)
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359042969

Dimensions

Dimensions	26 in x 0.75 in x 0.75 in
Height	0.75 in
Length	26 in
Length - Fuselink	26" (660.4mm)
Weight	0.235 lb
Width	0.75 in



Electrical Ratings

Amperage Rating	100 A
-----------------	-------

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	4800
Standard Package	10

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type K](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type K](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type K Solid & Removable HD](#)
- [Specifications - M100KA](#)
- [Test Documents - K Total Clear](#)
- [Test Documents - K Min Melt](#)