



# 100 A, Type QH Fuselinks, 23" Length, Solid Head

By CHANCE Utility  
Catalog # [M100QH23](#)

100 amp, Type QH Cutout fuselink with a 23" (584.2mm) pigtail.



### Features

- Comparable to Cooper/Kearney Type QA fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

|                            |   |
|----------------------------|---|
| Fuse Head Style            | Solid   |
| Fuselink Type              | Type QH                                       |
| Required Cutout Fuseholder | 100 Amp (Do not use in a 200 amp fuseholder.) |
| Type                       | Fuselinks                                     |
| UPC                        | 096359631910                                  |

### Dimensions

|                   |               |
|-------------------|---------------|
| Length - Fuselink | 23" (584.2mm) |
|-------------------|---------------|

### Electrical Ratings

|                 |       |
|-----------------|-------|
| Amperage Rating | 100 A |
|-----------------|-------|

### Logistics

|                  |      |
|------------------|------|
| Pallet Quantity  | 4800 |
| Standard Package | 10   |

### Product Assets

- [Catalogs - Fuse Links \(10B\)](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type QH](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type QH](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Type QH Fuse Links, Solid & Removable Head \(PSSAQHFUSELINK\)](#)
- [Test Documents - QH Total Clear](#)
- [Test Documents - QH Min Melt](#)



A proud member of the Hubbell Family.