



## 100 A, Type T (ANSI) Fuselinks, 23" Length, Solid Head

By Chance  
Catalog # [M100T23](#)

100 amp, Type T (ANSI) Cutout fuselink with a 23" (584.2mm) pigtail.

### Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

Catalog Number	M100T23
Fuse Head Style	Solid
Fuselink Type	Type T (ANSI)
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359043072

### Dimensions

Dimensions	23 in x 0.75 in x 0.75 in
Height	0.75 in
Length	23 in
Length - Fuselink	23" (584.2mm)



Weight	0.265 lb
Width	0.75 in

### Electrical Ratings

Amperage Rating	100 A
-----------------	-------

### Logistics

Pallet Quantity	4800
Standard Package	10

### Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type T](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type T](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Fuse Links, Type T Solid & Removable HD](#)
- [Specifications - M100T23](#)
- [Test Documents - T Total Clear](#)
- [Test Documents - T Min Melt](#)