



10 A, Type QH Fuselinks, 23" Length, Removable Head

By CHANCE Utility
Catalog # [M10QHA23](#)

10 amp, Type QH Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.



Features

- Comparable to Cooper/Kearney Type QA fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Fuse Head Style	Removable
Fuselink Type	Type QH
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359631071

Dimensions

Length - Fuselink	23" (584.2mm)
-------------------	---------------

Electrical Ratings

Amperage Rating	10 A
-----------------	------

Logistics

Pallet Quantity	4800 EA
Standard Package	10

Product Assets

- [Catalogs - Fuse Links \(10B\)](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type QH](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type QH](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Type QH Fuse Links, Solid & Removable Head \(PSSAQHFUSELINK\)](#)
- [Test Documents - QH Total Clear](#)
- [Test Documents - QH Min Melt](#)



A proud member of the Hubbell Family.