



12 A, Type K (ANSI) fuselinks, 23" Length, Solid Head

By CHANCE Utility
Catalog # [M12K23](#)

12 amp, Type K (ANSI) Cutout fuselink with a 23" (584.2mm) pigtail.



Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

| | |
|----------------------------|---|
| Fuse Head Style | Solid |
| Fuselink Type | Type K (ANSI) |
| Required Cutout Fuseholder | 100 Amp (Do not use in a 200 amp fuseholder.) |
| Type | Fuselinks |
| UPC | 096359043133 |

Dimensions

| | |
|-------------------|---------------|
| Length - Fuselink | 23" (584.2mm) |
| Weight | 0.059 lb |

Electrical Ratings

| | |
|-----------------|------|
| Amperage Rating | 12 A |
|-----------------|------|

Logistics

| | |
|------------------|------|
| Pallet Quantity | 4800 |
| Standard Package | 10 |

Product Assets

- [Catalogs - Fuse Links \(10B\)](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type K](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type K](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type K Solid & Removable HD \(PSSAKFUSELINK\)](#)
- [Test Documents - K Total Clear](#)
- [Test Documents - K Min Melt](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-M12K23-SPEC-EN | REV 4/2023