



## 12 A, Type T (ANSI) Fuselinks, 23" Length, Solid Head

By CHANCE Utility  
Catalog # [M12T23](#)

12 amp, Type T (ANSI) Cutout fuselink with a 23" (584.2mm) pigtail.



### Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

Fuse Head Style	Solid
Fuselink Type	Type T (ANSI)
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359043188

### Dimensions

Length - Fuselink	23" (584.2mm)
Weight	0.069 lb

### Electrical Ratings

Amperage Rating	12 A
-----------------	------

### Logistics

Pallet Quantity	4800
Standard Package	10

### Product Assets

[Catalogs - Fuse Links \(10B\)](#)  
[Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type T](#)  
[Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type T](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - Fuse Links, Type T Solid & Removable HD \(PSSATFUSELINK\)](#)  
[Test Documents - T Min Melt](#)  
[Test Documents - T Total Clear](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-M12T23-SPEC-EN | REV 1/2024