



## 140 A, Type K (ANSI) fuselinks, 23" Length, Solid Head

By CHANCE Utility  
Catalog # [M140K23](#)

140 amp, Type K (ANSI) Cutout fuselink with a 23" (584.2mm) pigtail.



### Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

Fuse Head Style	Solid
Fuselink Type	Type K (ANSI)
Required Cutout Fuseholder	200 Amp (Do not use in a 100 amp fuseholder.)
Type	Fuselinks
UPC	096359043355

### Dimensions

Length - Fuselink	23" (584.2mm)
Weight	0.892 lb

### Electrical Ratings

Amperage Rating	140 A
-----------------	-------

### Logistics

Pallet Quantity	2400
Standard Package	5

### Product Assets

[Catalogs - Fuse Links \(10B\)](#)  
[Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type K](#)  
[Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type K](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - Fuse Links, Type K Solid & Removable HD \(PSSAKFUSELINK\)](#)  
[Test Documents - K Total Clear](#)  
[Test Documents - K Min Melt](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-M140K23-SPEC-EN | REV 1/2024