



140 A, Type K (ANSI) fuselinks, 23"

Length, Solid Head

By Chance
Catalog # [M140K23T](#)

140 amp, Type K (ANSI) Cutout fuselink with a 23" (584.2mm) twin pigtail.

Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M140K23T
Fuse Head Style	Solid
Fuselink Type	Type K (ANSI)
Required Cutout Fuse holder	200 Amp (Do not use in a 100 amp fuseholder.)
Type	Fuselinks
UPC	096359799931

Dimensions

Length - Fuselink	23" (584.2mm)
Weight	0.98 lb



Electrical Ratings

Amperage Rating	140 A
-----------------	-------

Logistics

Pallet Quantity	2400
Standard Package	5

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type K](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type K](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type K Solid & Removable HD](#)
- [Specifications - M140K23T](#)
- [Test Documents - K Total Clear](#)
- [Test Documents - K Min Melt](#)



A Hubbell brand