




140 A, Type T (ANSI) Fuselinks, 26" Length, Removable Head

By Chance
Catalog # [M140TAT](#)

140 amp, Type T (ANSI) Cutout fuselink with a 26" (660.4mm) twin pigtail and a removable buttonhead.



Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M140TAT
Fuse Head Style	Removable
Fuselink Type	Type T (ANSI)
Required Cutout Fuse holder	200 Amp (Do not use in a 100 amp fuseholder.)
Type	Fuselinks

Dimensions

Length - Fuselink	26" (660.4mm)
-------------------	---------------

Electrical Ratings

Amperage Rating	140 A
-----------------	-------

Logistics

Standard Package	3
------------------	---

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type T](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type T](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type T Solid & Removable HD](#)
- [Test Documents - T Total Clear](#)
- [Test Documents - T Min Melt](#)



A Hubbell brand