




## 15 A, Type STH fuselinks, 23" Length, Removable Head

By Chance  
Catalog # [M15STHA23](#)

15 amp, Type STH Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.



### Features

- Comparable to S&C Standard Speed fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

Catalog Number	M15STHA23
Fuse Head Style	Removable
Fuselink Type	Type STH
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359630951

### Dimensions

Length - Fuselink	23" (584.2mm)
-------------------	---------------

### Electrical Ratings

Amperage Rating	15 A
-----------------	------

### Logistics

Carton Quantity	200
Pallet Quantity	4844
Standard Package	10

### Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type STH](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type STH](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Type Standard Fuse Links, Solid & Removable Head](#)
- [Test Documents - STH Total Clear](#)
- [Test Documents - STH Min Melt](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-M15STHA23-SPEC-EN | REV 6/2024