



1.0 A, Type Slo-Fast Fuselinks, 26" Length, Solid Head

By Chance
Catalog # M1D0SF

1.0 amp, Type SloFast Cutout fuselink with a 26" (660.4mm) pigtail.



Features

- Comparable to Cooper/Kearney Type X fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Dual element design specific for transformer protection
- Slow portion of time current characteristic curve closely matches transformers safe loading curve
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

| | |
|-----------------------------|---|
| Catalog Number | M1D0SF |
| Fuse Head Style | Solid |
| Fuselink Type | Type SloFast |
| Required Cutout Fuse holder | 100 Amp (Do not use in a 200 amp fuseholder.) |
| Type | Fuselinks |
| UPC | 096359042303 |

Dimensions

| | |
|-------------------|---------------|
| Length - Fuselink | 26" (660.4mm) |
| Weight | 0.176 lb |

Electrical Ratings

| | |
|-----------------|-----|
| Amperage Rating | 1 A |
|-----------------|-----|

Logistics

| | |
|------------------|------|
| Pallet Quantity | 4800 |
| Standard Package | 10 |

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type SloFast](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type SloFast](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type SF Solid & Removable HD](#)
- [Test Documents - SloFast Total Clear](#)
- [Test Documents - SloFast Min Melt](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-M1DOSF-SPEC-EN | REV 6/2024