



# 1 A, Type QH Fuselinks, 23" Length, Solid Head

By Chance  
Catalog # [M1QH23](#)

1 amp, Type QH Cutout fuselink with a 23" (584.2mm) pigtail.



## Features

- Comparable to Cooper/Kearney Type QA fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

## General

Catalog Number	M1QH23
Fuse Head Style	Solid
Fuselink Type	Type QH
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359631774

## Dimensions

Length - Fuselink	23" (584.2mm)
-------------------	---------------

## Electrical Ratings

Amperage Rating	1 A
-----------------	-----

## Logistics

Pallet Quantity	4800 EA
Standard Package	10

## Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type QH](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type QH](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Type QH Fuse Links, Solid & Removable Head](#)
- [Test Documents - QH Min Melt](#)
- [Test Documents - QH Total Clear](#)



A Hubbell brand