




## 1 A, Type STH fuselinks, 23" Length, Solid Head

By Chance  
Catalog # [M1STH23](#)

1 amp, Type STH Cutout fuselink with a 23" (584.2mm) pigtail.



### Features

- Comparable to S&C Standard Speed fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

|                             |   |
|-----------------------------|---|
| Catalog Number              | M1STH23                                       |
| Fuse Head Style             | Solid   |
| Fuselink Type               | Type STH                                      |
| Required Cutout Fuse holder | 100 Amp (Do not use in a 200 amp fuseholder.) |
| Type                        | Fuselinks                                     |
| UPC                         | 096359631323                                  |

### Dimensions

|                   |               |
|-------------------|---------------|
| Length - Fuselink | 23" (584.2mm) |
|-------------------|---------------|

### Electrical Ratings

|                 |     |
|-----------------|-----|
| Amperage Rating | 1 A |
|-----------------|-----|

### Logistics

|                  |      |
|------------------|------|
| Carton Quantity  | 200  |
| Pallet Quantity  | 4831 |
| Standard Package | 10   |

### Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type STH](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type STH](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Type Standard Fuse Links, Solid & Removable Head](#)
- [Test Documents - STH Total Clear](#)
- [Test Documents - STH Min Melt](#)



A Hubbell brand