




200 A, Type MS Fuseinks, 26" Length, Removable Head

By Chance
Catalog # [M200MSA](#)

200 amp, Type MS Cutout fuselink with a 26" (660.4mm) pigtail and a removable buttonhead.



Features

- Comparable to Cooper/Kearney Type KS fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Dual element design
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M200MSA
Fuse Head Style	Removable
Fuselink Type	Type MS
Required Cutout Fuse holder	200 Amp (Do not use in a 100 amp fuseholder.)
Type	Fuselinks
UPC	096359044635

Dimensions

Length - Fuselink	26" (660.4mm)
-------------------	---------------

Electrical Ratings

Amperage Rating	200 A
-----------------	-------

Logistics

Pallet Quantity	1440
Standard Package	3

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type MS](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type MS](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type MSA Removable HD](#)
- [Test Documents - MS Total Clear](#)
- [Test Documents - MS Min Melt](#)



A Hubbell brand