



2 A, Type STH fuselinks, 23" Length, Solid Head

By CHANCE Utility
Catalog # [M2STH23](#)

2 amp, Type STH Cutout fuselink with a 23" (584.2mm) pigtail.



Features

- Comparable to S&C Standard Speed fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

| | |
|----------------------------|---|
| Fuse Head Style | Solid |
| Fuselink Type | Type STH |
| Required Cutout Fuseholder | 100 Amp (Do not use in a 200 amp fuseholder.) |
| Type | Fuselinks |
| UPC | 096359631330 |

Dimensions

| | |
|-------------------|---------------|
| Length - Fuselink | 23" (584.2mm) |
|-------------------|---------------|

Electrical Ratings

| | |
|-----------------|-----|
| Amperage Rating | 2 A |
|-----------------|-----|

Logistics

| | |
|------------------|------|
| Carton Quantity | 200 |
| Pallet Quantity | 4833 |
| Standard Package | 10 |

Product Assets

[Catalogs - Fuse Links \(10B\)](#)
[Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type STH](#)
[Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type STH](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Type Standard Fuse Links, Solid & Removable Head \(PSSASTHFUSELINK\)](#)
[Test Documents - STH Total Clear](#)
[Test Documents - STH Min Melt](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-M2STH23-SPEC-EN | REV 1/2024