



30 A, Type T (ANSI) Fuselinks, 23" Length, Removable Head

By Chance
Catalog # [M30TA23](#)

30 amp, Type T (ANSI) Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.

Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M30TA23
Fuse Head Style	Removable
Fuselink Type	Type T (ANSI)
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359046806

Dimensions

Dimensions	23 in x 13.250 in x 4.120 in
Height	4.12 in
Length	23 in
Length - Fuselink	23" (584.2mm)

Weight	0.127 lb
Width	13.25 in

Electrical Ratings

Amperage Rating	30 A
-----------------	------

Logistics

Pallet Quantity	4800
Standard Package	10

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type T](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type T](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type T Solid & Removable HD](#)
- [Specifications - M30TA23](#)
- [Test Documents - T Total Clear](#)
- [Test Documents - T Min Melt](#)



A Hubbell brand