



# 15kV, 900 A, Single Insulator Load Break Disconnect

By Chance  
Catalog # [M3C159BN](#)

Single Insulator Load Break Disconnect Switch Type M3C.  
Electrical Ratings 15kV 110BIL 900A

## Features

- Fully Compliant with ANSI/IEEE C37.30.1
- 15, 27 & 38kV Voltage Classes
- 110, 125 and 150kV BIL Insulation Levels
- 600A & 900A Current Ratings
- Uses Chance Type C Polymer Cutout Insulator Assemblies
- Uses NEMA B Brackets for Cross Arm mounting
- Load Break Option Available

## General

Catalog Number           M3C159BN  
UPC                           096359732617

## Dimensions

Dimensions               20.000 in x 14.500 in x 6.750 in  
Height                    6.75 in  
Length                    20 in



\*Representative Image

Weight                    11.39 lb  
Width                    14.5 in

## Certifications And Compliance

Buy America(n) Qualified           TAA Compliant (All status valid till December 2024)

## Logistics

Pallet Quantity                       42

## Product Assets

- [Catalogs - Hookstick Operated Switches](#)
- [Installation Manuals - Type M3C Single Insulator Disconnect Switch for Distribution Switching](#)
- [Literature - Loadbreak M3C Single Insulator Disconnect](#)
- [Sales Drawings - PSSAM3C15-N](#)
- [Specifications - M3C159BN](#)