



15.5 kV, 110 kV BIL, 600 A, Porcelain (2 1/4" Bolt Circle) insulation, M3 Switch

By Chance
Catalog # [M3D62APR](#)

14.4kV, 110kV, 600 A, Single-Phase Hookstick Disconnect Switch.



*Representative Image

Features

- Fully Compliant with ANSI/IEEE C37.30.1
- 15, 27 & 38kV Voltage Classes
- 110, 125, 150, 200kV BIL Insulation Levels
- 600A & 900A Current Ratings
- Porcelain and ESP Polymer Insulator Assemblies with 2.25" Bolt Circles
- Distribution Base, Serrated Slots
- Load Break Option Available

General

| | |
|---------------------------------------|---|
| Base Type | Distribution Base, Serrated Slots |
| Blade Type | Solid Copper (two blade truss-member) |
| Cantilever Bending Strength - Routine | 1,200 Lbs (5.34 kN) |
| Catalog Number | M3D62APR |
| Color - Insulator | Sky Gray |
| Contact | Silver |
| Description - Terminal Connectors | 2 - Terminal Connectors (ATC1343, #2 - 500kcmil) w/ galvanized hardware |
| Insulator Type | Porcelain (2 1/4" Bolt Circle) |
| Material - Base | Galvanized Steel per ASTM A153 |
| Tension Range | 5000 lb |
| Torsional Strength | 3,000 in Lbs (339 N-M) |

Dimensions

| | |
|-------------|-------|
| Bolt Length | 10 in |
|-------------|-------|

Electrical Ratings

| | |
|--|--------------------|
| Arc Distance - Dry | 6" (152.4mm) |
| BIL | 110 kV |
| Creep and Leakage Distance | 10.5" (266.7mm) |
| Current Overload - 8hr Emergency | 1080 A |
| Current Rating | 600 A |
| Dead-Ending Rating - Working Load | 8,000 Lbs |
| Reference Voltage Limit - Minimum | 14.4kV |
| Temperature Rise - Max. at 600A | 28°C |
| Voltage - Maximum | 15.5 kV |
| Withstand Current - Short Time (10 cycles) | 40kA, asymmetrical |
| Withstand Current - Short Time (2 sec) | 25kA, symmetrical |
| Withstand Current - Short Time (3 sec) | 16kA, symmetrical |

Certifications And Compliance

| | |
|----------------------|------------------------------------|
| Industry Standard(s) | All Applicable ANSI/IEEE Standards |
|----------------------|------------------------------------|

Logistics

| | |
|------------------|-------|
| Pallet Quantity | 42 EA |
| Standard Package | 1 |

Product Assets

- [Catalogs - Hookstick Operated Switches](#)
- [Installation Manuals - Type M3C Single Insulator Disconnect Switch for Distribution Switching](#)
- [Installation Manuals - Instructions for CHANCE Type M3 Distribution Switch](#)
- [Literature - SA-M3D_C](#)
- [Sales Drawings - Type M3 Switch](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-M3D62APR-SPEC-EN | REV 6/2024