



## 3 A, Type K (ANSI) fuselinks, 23" Length, Solid Head

By Chance  
Catalog # [M3K23](#)

3 amp, Type K (ANSI) Cutout fuselink with a 23" (584.2mm) pigtail.



### Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

Catalog Number	M3K23
Fuse Head Style	Solid
Fuselink Type	Type K (ANSI)
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359046462

### Dimensions

Dimensions	23 in x 14.500 in x 4.120 in
Height	4.12 in
Length	23 in
Length - Fuselink	23" (584.2mm)
Weight	0.059 lb
Width	14.5 in

### Electrical Ratings

Amperage Rating	3 A
-----------------	-----

### Logistics

Pallet Quantity	4800
Standard Package	10

### Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type K](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type K](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Fuse Links, Type K Solid & Removable HD](#)
- [Test Documents - K Total Clear](#)
- [Test Documents - K Min Melt](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-M3K23-SPEC-EN | REV 6/2024