




## 40 A, Type MS Fuseinks, 26" Length, Removable Head

By Chance  
Catalog # [M40MSA](#)

40 amp, Type MS Cutout fuselink with a 26" (660.4mm) pigtail and a removable buttonhead.



### Features

- Comparable to Cooper/Kearney Type KS fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Dual element design
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

Catalog Number	M40MSA
Fuse Head Style	Removable
Fuselink Type	Type MS
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359047223

### Dimensions

Length - Fuselink	26" (660.4mm)
-------------------	---------------

### Electrical Ratings

Amperage Rating	40 A
-----------------	------

### Logistics

Carton Quantity	200
Pallet Quantity	4800
Standard Package	10

### Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type MS](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type MS](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Fuse Links, Type MSA Removable HD](#)
- [Test Documents - MS Total Clear](#)
- [Test Documents - MS Min Melt](#)



A Hubbell brand