



## 40 A, Type MS Fuseinks, 23" Length, Removable Head

By CHANCE Utility  
Catalog # [M40MSA23](#)

40 amp, Type MS Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.



### Features

- Comparable to Cooper/Kearney Type KS fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Dual element design
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

Fuse Head Style	Removable
Fuselink Type	Type MS
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359047230

### Dimensions

Length - Fuselink	23" (584.2mm)
Weight	0.137 lb

### Electrical Ratings

Amperage Rating	40 A
-----------------	------

### Logistics

Pallet Quantity	4800
Standard Package	10

### Product Assets

[Catalogs - Fuse Links \(10B\)](#)  
[Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type MS](#)  
[Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type MS](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - Fuse Links, Type MSA Removable HD \(PSSAMSAFUSELINK\)](#)  
[Technical Solutions - CH-M40MSA23-SPEC-EN](#)  
[Test Documents - MS Min Melt](#)  
[Test Documents - MS Total Clear](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-M40MSA23-SPEC-EN | REV 1/2024