




40 A, Type STH fuselinks, 23" Length, Removable Head

By Chance
Catalog # [M40STHA23](#)

40 amp, Type STH Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.



Features

- Comparable to S&C Standard Speed fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M40STHA23
Fuse Head Style	Removable
Fuselink Type	Type STH
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359630982

Dimensions

Length - Fuselink	23" (584.2mm)
-------------------	---------------

Electrical Ratings

Amperage Rating	40 A
-----------------	------

Logistics

Carton Quantity	200
Pallet Quantity	4852
Standard Package	10

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type STH](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type STH](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Type Standard Fuse Links, Solid & Removable Head](#)
- [Test Documents - STH Total Clear](#)
- [Test Documents - STH Min Melt](#)



A Hubbell brand