



Pole Clamp Only, 2"

By CHANCE Utility
Catalog # [M47412](#)

Chance Pole Type Wire Tong Saddles are made of lightweight aluminum for handling ease. These rugged heat-treated saddles will support a maximum of 1000 pounds (450kg) without the extension. The clamp is set far enough away from the base to give ample clearance for most jobs. Where additional clearance is required, the Chance Wire Tong Saddle Extension can be easily bolted to the saddle. This heat-treated aluminum-alloy extension is 4 inches (100mm) long and has a tested working load rating of 800 pounds (360kg). The Wheel Type fasteners are easy to apply, hold the saddle firmly in place, and prevent riding down and excessive play. The Wheel Tightener has the advantage of being able to fit into close places such as between crossarm braces, under guy wires, etc.



General

Style	Pole Clamp Only
Type	Wire Tong
UPC	096359048190

Dimensions

Dimensions	6.25 in x 5.56 in x 5.5 in
Height	5.5 in
Length	6.25 in
LengthMetric	15.875 mm
Weight	2 lb
WeightMetric	0.90718474 kg
Width	5.56 in

Logistics

Pallet Quantity	343
-----------------	-----

Product Assets

[Catalogs - Conductor Support Equipment \(2200\)](#)
[Sales Drawings - SA_M4740-3W](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-M47412-SPEC-EN | REV 8/2023