



50 A, Type K (ANSI) fuselinks, 23" Length, Solid Head

By CHANCE Utility
Catalog # [M50K23](#)

50 amp, Type K (ANSI) Cutout fuselink with a 23" (584.2mm) pigtail.



Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Fuse Head Style	Solid
Fuselink Type	Type K (ANSI)
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359048725

Dimensions

Length - Fuselink	23" (584.2mm)
Weight	0.127 lb

Electrical Ratings

Amperage Rating	50 A
-----------------	------

Logistics

Pallet Quantity	4800
Standard Package	10

Product Assets

[Catalogs - Fuse Links \(10B\)](#)
[Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type K](#)
[Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type K](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Fuse Links, Type K Solid & Removable HD \(PSSAKFUSELINK\)](#)
[Technical Solutions - CH-M50K23-SPEC-EN](#)
[Test Documents - K Total Clear](#)
[Test Documents - K Min Melt](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-M50K23-SPEC-EN | REV 1/2024