



# 50 A, Type K (ANSI) fuselinks, 23" Length, Removable Head

By Chance  
Catalog # [M50KA23](#)

50 amp, Type K (ANSI) Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.

## Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

## General

Catalog Number	M50KA23
Fuse Head Style	Removable
Fuselink Type	Type K (ANSI)
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359048701

## Dimensions

Dimensions	23 in x 13.250 in x 5.000 in
Height	5 in
Length	23 in
Length - Fuselink	23" (584.2mm)



Weight	0.127 lb
Width	13.25 in

## Electrical Ratings

Amperage Rating	50 A
-----------------	------

## Logistics

Pallet Quantity	4800
Standard Package	10

## Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type K](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type K](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Fuse Links, Type K Solid & Removable HD](#)
- [Specifications - M50KA23](#)
- [Test Documents - K Total Clear](#)
- [Test Documents - K Min Melt](#)