



50 A, Type STH fuselinks, 23" Length, Solid Head

By CHANCE Utility
Catalog # [M50STH23](#)

50 amp, Type STH Cutout fuselink with a 23" (584.2mm) pigtail.



Features

- Comparable to S&C Standard Speed fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Fuse Head Style	Solid
Fuselink Type	Type STH
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359631439

Dimensions

Length - Fuselink	23" (584.2mm)
-------------------	---------------

Electrical Ratings

Amperage Rating	50 A
-----------------	------

Logistics

Carton Quantity	200
Pallet Quantity	4853
Standard Package	10

Product Assets

[Catalogs - Fuse Links \(10B\)](#)
[Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type STH](#)
[Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type STH](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Type Standard Fuse Links, Solid & Removable Head \(PSSASTHFUSELINK\)](#)
[Test Documents - STH Total Clear](#)
[Test Documents - STH Min Melt](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-M50STH23-SPEC-EN | REV 1/2024