



5 A, Type STH fuselinks, 23" Length, Removable Head

By CHANCE Utility
Catalog # [M5STHA23](#)

5 amp, Type STH Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.



Features

- Comparable to S&C Standard Speed fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

| | |
|----------------------------|-----------------------------------------------|
| Fuse Head Style | Removable |
| Fuselink Type | Type STH |
| Required Cutout Fuseholder | 100 Amp (Do not use in a 200 amp fuseholder.) |
| Type | Fuselinks |
| UPC | 096359630555 |

Dimensions

| | |
|-------------------|---------------|
| Length - Fuselink | 23" (584.2mm) |
|-------------------|---------------|

Electrical Ratings

| | |
|-----------------|-----|
| Amperage Rating | 5 A |
|-----------------|-----|

Logistics

| | |
|------------------|------|
| Pallet Quantity | 4800 |
| Standard Package | 10 |

Product Assets

- [Catalogs - Fuse Links \(10B\)](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type STH](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type STH](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Type Standard Fuse Links, Solid & Removable Head \(PSSASTHFUSELINK\)](#)
- [Test Documents - STH Total Clear](#)
- [Test Documents - STH Min Melt](#)



A proud member of the Hubbell Family.