



## 60 A, Type QH Fuselinks, 23" Length, Solid Head

By CHANCE Utility  
Catalog # [M60QH23](#)

60 amp, Type QH Cutout fuselink with a 23" (584.2mm) pigtail.



### Features

- Comparable to Cooper/Kearney Type QA fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

### General

Fuse Head Style	Solid
Fuselink Type	Type QH
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359631897

### Dimensions

Length - Fuselink	23" (584.2mm)
-------------------	---------------

### Electrical Ratings

Amperage Rating	60 A
-----------------	------

### Logistics

Pallet Quantity	4800
Standard Package	10

### Product Assets

[Catalogs - Fuse Links \(10B\)](#)  
[Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type QH](#)  
[Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type QH](#)  
[Literature - Switching Line Card\\_FAQ\\_2019](#)  
[Sales Drawings - Type QH Fuse Links, Solid & Removable Head \(PSSAQHFUSELINK\)](#)  
[Test Documents - QH Total Clear](#)  
[Test Documents - QH Min Melt](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-M60QH23-SPEC-EN | REV 1/2024