



60 A, Type QH Fuselinks, 23" Length, Removable Head

By CHANCE Utility
Catalog # [M60QHA23](#)

60 amp, Type QH Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.



Features

- Comparable to Cooper/Kearney Type QA fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Fuse Head Style	Removable
Fuselink Type	Type QH
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359631149

Dimensions

Length - Fuselink	23" (584.2mm)
-------------------	---------------

Electrical Ratings

Amperage Rating	60 A
-----------------	------

Logistics

Pallet Quantity	4800
Standard Package	10

Product Assets

[Catalogs - Fuse Links \(10B\)](#)
[Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type QH](#)
[Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type QH](#)
[Literature - Switching Line Card_FAQ_2019](#)
[Sales Drawings - Type QH Fuse Links, Solid & Removable Head \(PSSAQHFUSELINK\)](#)
[Test Documents - QH Total Clear](#)
[Test Documents - QH Min Melt](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-M60QHA23-SPEC-EN | REV 1/2024