



6 A, Type K (ANSI) fuselinks, 26" Length, Removable Head

By Chance
Catalog # [M6KA](#)

6 amp, Type K (ANSI) Cutout fuselink with a 26" (660.4mm) pigtail and a removable buttonhead.

Features

- Fully Compliant with ANSI/IEEE C37.42 - 2016
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M6KA
Fuse Head Style	Removable
Fuselink Type	Type K (ANSI)
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359048886

Dimensions

Length - Fuselink	26" (660.4mm)
Weight	0.078 lb

Electrical Ratings



Amperage Rating	6 A
-----------------	-----

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	4800
Standard Package	10

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type K](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type K](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type K Solid & Removable HD](#)
- [Specifications - M6KA](#)
- [Test Documents - K Total Clear](#)
- [Test Documents - K Min Melt](#)



A Hubbell brand